

## Installation Instructions for PERMALIGHT<sup>®</sup> Safety Foam Guards

### Self-Adhesive Safety Foam Guard Instructions



#### Product Preparation

- **For 16' long safety foam guard** - \*This will arrive in a tightly coiled roll for the ease of shipping (our standard 39-3/8" safety foam guards are shipped flat). The **night before installation**, please completely unroll the foam guard and lay it out in a straight line at room temperature. This will ensure your product will be straight and ready to be cut and installed by the next morning.
- **CUTTING (Optional)** - If you need to cut a safety foam guard to a specific length, you can do so using a utility knife with a new blade.
  - a. Hold the safety foam guard in place (**without** removing the silicone film protecting the adhesive), measure, mark the length and cut to the desired length with the utility knife.
  - b. For **high-volume cutting projects**, we recommend the **Slat Cutter** (SKU: 82-5901) or the **Compact Foam Guard Cutting Machine** (SKU: 82-5902)

#### CUTTING TOOL OPTIONS:



UTILITY KNIFE



or SLAT CUTTER



or COMPACT CUTTING MACHINE

#### Surface Preparation

PERMALIGHT<sup>®</sup> self-adhesive Safety Foam Guards come with a strong self-adhesive backing. Even if an installation surface looks clean, it may have accumulated a layer of dust or grimy sheen from wear and dirt in the installation environment. Here are a few easy steps that will ensure a long-term bond.

1. **CLEAN** - Wipe the installation surface with a water-moistened microfiber cloth.
  - a. For grimmer surfaces, use a separate isopropyl alcohol-dampened microfiber cloth and wipe the installation surface a second time. **Please wait until all liquid has fully evaporated before moving on to the next step.**
2. **ADHERE** - Without touching the adhesive, remove the covering from the adhesive backing.

- a. Hold the foam guard along its sides to keep the strong adhesive free of residue from hands and fingers.
3. **APPLY** - Firmly press/apply the foam guard in place. **Do not pull it off to re-align or re-adjust.** The self-adhesive is its strongest when it is pressed in the right spot on the first application.
  - a. **Warning: any removing and re-applying will decrease the adhesive's strength and weaken the initial strongest bond.**

## Non-Adhesive Safety Foam Guard Instructions



PERMALIGHT® Types B/B+ are non-adhesive and are designed to snugly slide onto an I-beam.

1. Wipe over the installation surface with a water-moistened microfiber cloth
2. Press Types B or B+ onto the dry I-beam projection for a tight fit
  1. If you want to increase the snug fit, you may use our optional 3M Adhesive (SKU: 83-0789). Please note that this adhesive is flammable and only ships via **UPS Ground**.

## Steel Support Safety Foam Guard Instructions



PERMALIGHT® Safety Foam Guards with Stainless Steel Support come with pre-attached, hardy metal support. The stainless-steel backing has six holes for screw-mounting to surfaces. Each stainless-steel supported Foam Guard comes with six screws and six anchors.

## Magnetic Safety Foam Guard Instructions



PERMALIGHT® Magnetic Safety Foam Guards are ideal in situations where you want to reposition the Safety Padding. The magnet-supported safety foam guards stick well to any magnetic-compatible surfaces, such as metal filing cabinets, racks, shelves, machinery, and equipment.

***Have questions or comments?***

Visit us at [AmericanPermalight.com](http://AmericanPermalight.com) or send us an email at [info@AmericanPermalight.com](mailto:info@AmericanPermalight.com)